

Part Number : 2240911064
Product Description : CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.25mm Pitch, Single Row, 600.00mm Length, 6 Circuits, White
Series Number : 224091
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2240911064_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224091
Description	CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.25mm Pitch, Single Row, 600.00mm Length, 6 Circuits, White
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	CLIK-Mate-to-CLIK-Mate
Product Name	CLIK-Mate
Type	Discrete Wire Assembly
UPC	196823353161

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Cable Length	600.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	White
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester

Downloaded from Arrow.com.

Net Weight	7.856/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, Tin Plating, 6 Circuits	5023820670
1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Right-Angle, Tin (Sn) Plating, 6 Circuits	5023860670

Downloaded from Arrow.com.