



+ RELAYS, CONTACTORS & SWITCHES
DIP & SIP SWITCHES



✓ Active

TE CONNECTIVITY (TE)
8136-475G7=JUMPER PLUG ASSY
[Alcoswitch](#) | [Alcoswitch DIP](#) , [Alcoswitch DIP JUMPER PLUG](#)

8136-475G7
TE Internal Number: 1-1437507-7

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)
Product Type Jumper Plug Assembly
Operating Temperature Range (°C) -65 – 125
Voltage Rating (VDC) 500
Centerline 2.54 mm [.1 in]

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Plug Assy

PDF (TIFF AVAILABLE)

English

Product Environmental Compliance

TE Material Declaration

MD_1-1437507-7_11302015814_dmtec

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features	
Product Type	Jumper Plug Assembly
Electrical Characteristics	
Voltage Rating (VDC)	500
Housing Features	
Centerline	2.54 mm [.1 in]
Usage Conditions	
Operating Temperature Range (°C)	-65 – 125
Other	
Comment	2x10

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance

PDF