



Part Number : [191890008](#)

Series Number : 19189

Product Category : Splices

Product Description : Krimptite Butt Splice for 14-16 AWG Wire

Status : Active

Engineering Number : B-131

Documents & Resources

Drawings

[Drawing 191890008_sd.pdf](#)


Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)4144-DC (27 June 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Splices |
| Series | 19189 |
| Description | Krimptite Butt Splice for 14-16 AWG Wire |
| Product Family | Splices |
| Product Name | Butt,Krimptite |
| UPC | 800755048803 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

Physical

| | |
|--------------------------------|---------|
| Barrel Type | Closed |
| Insulation | None |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.943/g |
| Packaging Type | Bag |
| Wire Size (AWG) | 14, 16 |

Application Tooling

Global

| Description | Part Number |
|--|------------------|
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ² | <u>640030100</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <u>640070100</u> |
| ServiceGrade Hand Crimp Tool - Ratchet | <u>640160038</u> |

This document was generated on Jul 29, 2024