molex
one company > a world of innovation

This document was generated on 02/05/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1201080389

Status: Active

Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 65.0m (213.25') Length, 6.99mm (.275") Diameter, Teal

Replacement Part Number : http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=13004803231300480323 (drop-in)

Documents:
Drawing (PDF) RoHS Certificate of Compliance (PDF)

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free Status
Not Reviewed
For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
120108 Series

Agency Certification	
UL	E361772
General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Performance Category	5e
Product Name	Micro-Change (M12)
Protocol	EtherNet
Replacement Part Number	1300480323 (drop-in)
Type	Double Ended
UPC	78172543404
Physical	
Cable Diameter	6.99mm (.275")
Cable Length	65.0m (213.25')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +75°C
Wire Size AWG	24
Wire/Cable Type	TPE
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Material Info	
Engineering Number	E11A06007M650
Reference - Drawing Numbers	
Sales Drawing	SD-120108-057

Downloaded from Arrow.com.

This document was generated on 02/05/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.