




LEAD FREE PART NUMBER


SHELL	A \pm 0.38	B \pm 0.12	C \pm 0.10	D \pm 0.25	E \pm 0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S82C4PA00	D09S82C6PA00
15	39.14	33.32	26.32	24.54	19.18	D15S82C4PA00	D15S82C6PA00
25	53.03	47.04	40.04	38.25	33.12	D25S82C4PA00	D25S82C6PA00
37	69.32	63.50	56.50	54.71	49.68	D37S82C4PA00	D37S82C6PA00
						Gold flash	0.76 μ gold




view shown without plastic pin



PC card drilling dimensions(after plating)
(thickness 1.60 or 2.40±0.20mm)



Detail of integral plastic pin



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code		surface		tolerance		projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			
M	ELX-I-18050	MP	2014/06/23	angles	linear	.0±0.1 .00±0.1 .000±0.1	MM
							scale 2:1
				dr	PESSON	1994/02/01	
				engr	MITHUN PAUL	2014/06/23	dwg no
				chr	ALIAS BABU	2014/06/23	sheet 1 of 1
				appd	BIJU K PAUL	2014/06/23	size
							FCI
							C01-8646-0219
							A3
							type
							Product Customer Drawing