



Part Number : [745460402](#)

Product Description : iPass PCIe x4 Cable Assembly, 28 AWG, 2.0m Length

Series Number : 74546

Status : New Business Not Supported

Product Category : High-Speed I/O Cable Assemblies



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	High-Speed I/O Cable Assemblies
Series	74546
Description	iPass PCIe x4 Cable Assembly, 28 AWG, 2.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Product Family	iPass Connector System
Product Name	iPass,PCI Express
Type	Pluggable
UPC	822348864836

Agency

CSA	LR64395
UL	E72548

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V DC

Physical

Cable Bundling	None
Cable Length	2.0m
Circuits (Loaded)	38
Circuits (maximum)	38
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	267.892/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Waterproof / Dustproof	Yes
Wire/Cable Type	Round
Wire Insulation Diameter	N/A

Wire Size (AWG)	28
-----------------	----

This document was generated on Sep 20, 2024