

14-Outlet Economy Network Server Surge Protector, 15 ft. (4.57 m) Cord, 3000 Joules, 1U Rack-Mount

MODEL NUMBER: DRS-1215



Highlights

- 14 outlets / 15-ft. (4.57 m) cord
- 3000 joule rating
- Adjustable rackmount hardware

Package Includes

- DRS-1215 Surge Suppressor
- Warranty information
- Instruction manual

Description

Tripp Lite's DRS-1215 offers surge and noise suppression in a versatile all-metal multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Includes 14 outlets (6 front/8 rear), 15-ft. (4.57 m) AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LED indicates surge protection status.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 14 NEMA5-15R (6 front & 8 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3000 joules

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- 3000 joules AC surge suppression with EMI/RFI filtering
- 14 NEMA 5-15R output receptacles (6 front/8 rear)
- 15-ft. (4.57 m) AC cord with NEMA 5-15P straight-in plug connection
- Diagnostic LED confirms suppressor operation
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW

UPC Code	037332100245
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Circuit Breaker (amps)	15
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Power switch controls power to all outlets
Diagnostic LED Details	Green - Protection Present
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3000
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Housing Color	Black
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 38.9mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	9.30 x 2.50 x 20.40
Shipping Dimensions (hwd / cm)	23.62 x 6.35 x 51.82
Shipping Weight (lbs.)	5.86
Shipping Weight (kg)	2.66
Unit Dimensions (hwd / in.)	1.750 x 17.500 x 4.000
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); UL 1363
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EATON**

1000 Eaton Boulevard

Cleveland, OH 44122

United States

TRIPP-LITE

by **EATON**

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.