
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A3	NEW RELEASE	22/June/2022	
A4	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80° C 300V
24AWG VW-1 LL84201 CSA AWM I/II A 80° C 300V 24AWG FT1 COPARTNER



PIN OUT

INNER LAYER CODE			OUTER LAYER CODE		
P1	P2		P1	P2	
1	1	BLACK	23	23	BLACK
2	2	BROWN	24	24	BROWN
3	3	RED	25	25	RED
4	4	ORANGE	26	26	ORANGE
5	5	YELLOW	27	27	YELLOW
6	6	GREEN	28	28	GREEN
7	7	BLUE	29	29	BLUE
8	8	PURPLE	30	30	PURPLE
9	9	GREY	31	31	GREY
10	10	WHITE	32	32	WHITE
11	11	PINK	33	33	PINK
12	12	LIGHT GREEN	34	34	LIGHT GREEN
13	13	BLACK/WHITE	35	35	BLACK/WHITE
14	14	BROWN/WHITE	36	36	BROWN/WHITE
15	15	RED/WHITE	37	37	RED/WHITE
16	16	ORANGE/WHITE	38	38	ORANGE/WHITE
17	17	GREEN/WHITE	39	39	GREEN/WHITE
18	18	BLUE/WHITE	40	40	BLUE/WHITE
19	19	PURPLE/WHITE	41	41	PURPLE/WHITE
20	20	RED/BLACK	42	42	RED/BLACK
21	21	ORANGE/BLACK	43	43	ORANGE/BLACK
22	22	YELLOW/BLACK	44	44	YELLOW/BLACK
			SHELL	SHELL	DRAIN WIRE

NOTE:
1. TESTING CONDITIONS:
   A: INSULATION RESISTANCE: 10MΩ
   B: VOLTAGE: DC300V/0.01S
   C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDHD44MF0-001.5	1.5FT±0.8inch	457±20mm
CS-DSDHD44MF0-002.5	2.5FT±1inch	762±25mm
CS-DSDHD44MF0-005	5FT±2inch	1524±51mm
CS-DSDHD44MF0-010	10FT±3inch	3048±76mm
CS-DSDHD44MF0-015	15FT±3inch	4572±76mm
CS-DSDHD44MF0-025	25FT±4inch	7620±102mm
CS-DSDHD44MF0-050	50FT±8inch	15240±203mm

NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS		ANGLES
.X	±.X	± X°
.XX	±.XX	
.XXX	±.XXX	

THIRD ANGLE PROJECTION

EAR NO.

APPROVALS	DATE
DRAWN XF	
CHECKED HYJ	
RESP ENG	
MFG ENG	

CAD FILE:

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

DELUXE, HD44 M/F MOLDED XX

SIZE	DWG. NO.	REV.
A	CS-DSDHD44MF0-XXX	A4

SCALE: N/A SHEET 1 OF 1

Downloaded from Arrow.com.