



Part Number : 1301250001

Series Number : 130125

Product Category : Festoons

Product Description : Wire Rope Festoon Car Round, 23.11mm (.910") Cable Height - Maximum

Status : Active

Engineering Number : 5121

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Festoons
Series	130125
Description	Wire Rope Festoon Car Round, 23.11mm (.910") Cable Height - Maximum
Component Type	Car - Intermediate

Product Name	Aero-Motive
Type	Wire Rope
UPC	78678805121

## Physical

Cable Height - Maximum	23.11mm (.910")
Combined Cable Weight-Max./Car	4.08kg (9.0 lb)
Depth	51.40mm (2.024")
Duty	Light
Height	127.00mm (5.000")
Length	86.25mm (3.400")
Material - Metal	N/A
Material - Resin	Nylon
Material - Wheel	Steel - Sealed Ball Bearing
Net Weight	174.632/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	N/A
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Round

---



---

This document was generated on Jul 07, 2024