

UTP28SP6BU

Category 6 Performance, 28 AWG UTP patch cord with TX6™ Modular Plugs on each end. Blue, 6 ft.

Specs | Packaging Details | Documents

Add to Favorites Add to BOM

Performance Level	Category 6
Cable Type	U/UTP
Cable Color	Blue
Length (ft.)	6.00
Length (m)	1.8
Flammability Rating	CM, LSZH-1 (60332-1)
Termination End 1	Modular Plug
Termination End 2	Modular Plug
Standards	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
CE Compliant	Yes
Nominal Cable O.D. (In.)	0.15
Nominal Cable O.D. (mm)	3.8
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
AWG Size	28
BMEcat - Type of Connector	RJ45 8(8)
Boot Color	Clear
Conductor Material	Copper
Conductor Type	Stranded
Installation Temperature	-40°F to 158°F (-40°C to 70°C)
Material	Copper
Operating Temperature	14°F to 167°F (-10°C to 75°C)
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

Downloaded from Arrow.com.