
44A1141-22-9/9/9/9-9 Product Details



Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A1141-22-9/9/9/9-9

44A1141-22-9/9/9/9-9

TE Internal Number: 3820653001

Product Highlights View All

- Cable Type = Spec 44
- Wire Source = United Kingdom
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Cable Type	Spec 44
Cable Style	Jacketed, Round-Braid Shielded

Electrical Characteristics

Voltage Rating (VAC)	600

Dimensions

Conductor Outer Diameter (mm [in])	0.79 [0.031]
Shield (Screen) Diameter (mm [in])	3.56 [0.140]

Body Features

Wire Size (AWG/CM)	22 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	White
Nominal Outside Diameter (mm [in])	3.96 [0.156]
Wire Diameter (mm [in])	1.19 [0.0468]

Configuration Features

Number of Conductors	Twisted Quad

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	-65 – +150
Wire Size - Details	22 AWG 0.38 mm², 0.00059 in², 19 x 34 AWG

Operation/Application

Application	General Purpose - Light Weight

Packaging Features

Wire Source	United Kingdom

Other

Brand	Raychem
Node Classification	Multicore Cable

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved | Provide Website Feedback

Feedback

Downloaded from Arrow.com.