


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210370035](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Poles Plus Ground with C4 Circuit, Yellow LED, Black, Nitrile Gasket



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	121037
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906484507
Physical	
Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	5.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	E850B0
Reference - Drawing Numbers	
Sales Drawing	SD-121037-002

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - ED/01/2017 (12 January 2017) 2,4-di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p	China RoHS
Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121037](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION