



Part Number : [2177961032](#)

Product Description : KK 254-to-KK 254 Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 300.00mm Length, 3 Circuits, Natural

Series Number : 217796

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[2177961032 sd.pdf](#)


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217796
Description	KK 254-to-KK 254 Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 300.00mm Length, 3 Circuits, Natural
Assembly Configuration	Dual Ended Connectors
Connector to Connector	KK 254-to-KK 254
Product Name	KK 254
Type	Discrete Wire Assembly
UPC	195842122819

Physical

Cable Length	300.00mm
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural (White)
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon

Net Weight	5.110/g
Number of Rows	1
Pitch - Mating Interface	2.54mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Vertical Breakaway Headers with Friction Lock	<u>42375</u>
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	<u>42377</u>
KK 254 Right-Angle Breakaway Headers	<u>42376</u>
KK 254 Single Row Vertical Headers	<u>4030</u>
KK 254 Vertical Single Row Solid Headers	<u>6373</u>
KK 254 Vertical Single Row Headers	<u>6410</u>
KK 254 RPC Vertical Headers with Friction Lock	<u>171856</u>
KK 254 RPC Right-Angle Headers with Friction Lock	<u>171857</u>

This document was generated on May 06, 2026