



Search:

Go

[Products](#)[Catalogs](#)[Search](#)[Customer Support](#)[About Cannon](#)[Home](#)

Plastic / Metal Coupling / Sealed

PART NUMBER: 192900-0000

[Sales Support](#)[Ask a Specialist](#)[Product Home](#)[Stock Check](#)

Product Family	Trident
Product Group	Neptune, TNM, Multiway, Ringlock, Snap Together, Contact
Component	Contact
Packaging	Reeled (3000)
Contact Finish	Tin
Contact Type	Stamped
Type of Contact	Pin
Wire Range mm²	0,50 - 1,50
Wire Size	20-16 AWG
Contact Material	Copper Alloy
Contact Current Rating	16 A
Contact Resistance	5 m ohms
Mating Cycles	200 Insertions
Contact Retention (minimum)	67 N
Retention Spring Material	Brass
For more information	Contact Cannon Sales Department
Nomenclature	T2P16MC4ST
Insulation Diameter	Ø2,00 (.078) - 3,00 (.118)
Strip Length	3,95 ±0,25 (.155 ±.009)
Footnote	Dimensions are in mm (inch). Dimensions are subject to change.

[Sign In](#) | [Contact Us](#) | [Legal Disclaimer](#) | [Privacy Policy](#) | [Home](#)

© 2006 ITT Industries