Data Sheet | Item Number: 756-3204/190-150
Connecting cable; 19-pole; Length: 15 m
https://www.wago.com/756-3204/190-150


DISCONTINUED:
01.01.2027




Pin 6, 12, 19: 1,00 mm²;
Pin 1 - 5, 7 - 11, 13 - 19: 0,34 mm²

1	violett	11	schwarz
2	rot	12	grün-gelb
3	grau	13	gelb-braun
4	rot-blau	14	braun-grün
5	grün	15	weiß
6	blau	16	gelb
7	grau-rosa	17	rosa
8	weiß-grün	18	grau-braun
9	weiß-gelb	19	braun
10	weiß-grau		

Color: ■ black





Dimensions in mm

Technical data	
Connection type	M23 socket - free end
Pole number	19
Cable connection direction to mating direction	90 °
Cable length	15 m
Operating voltage	≤ 300 V
Operating current	8 A
Operating current	10 mm² 1 A
Rated impulse withstand voltage	≥ 2.0 kV rms

Downloaded from Arrow.com.

Mechanical data

Bending cycles	2 million
Drag chain capability	Yes
Weight	2152 g
Color	black

Environmental requirements

Ambient (operating) temperature (dynamic)	-25 … +80 °C
Ambient (operating) temperature (static)	-40 … +90 °C
Protection type	IP67

Commercial data

Product Group	23 (I/O passive and accessories)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918569095
Customs tariff number	85444290900
End of Sale	2027-01-01
End of Production	2027-01-02
End of Delivery	2027-03-01
End of Service and Repair	2027-07-01

Product Classification

UNSPSC	26121629
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 9.0	EC001855
ETIM 10.0	EC001855
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-3204/190-150

Downloaded from Arrow.com.

Documentation

System Description

Sensor/Actuator Boxes – General Product Information	pdf 428.34 KB	

CAD/CAE-Data

CAE data

WSCAD Universe 756-3204/190-150	

Downloaded from Arrow.com.