



Have a Question?

Chat with a Product Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Input/Output (Box to Box) > Product Feature Selector > Product Details

2227667-1 Product Details

Share Print Email

2227667-1

TE Internal Number: 2227667-1

Preliminary

View 3D PDF

Pluggable Connectors, Cages & Accessories

Not reviewed for RoHS Compliance

Product Highlights:

- zQSFP+ Product Line
- Cage Assembly with Integrated Connector
- zQSFP+ Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information	
Product Drawings: CAGE AND CONNECTOR ASSEMBLY, WITH EMI SPRING, THRU B... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version 1) 3D Model (IGES, Version 1) 3D Model (STEP, Version 1) List all Documents	Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Line = zQSFP+ - Product Type = Cage Assembly with Integrated Connector Mechanical Attachment: - PCB Mount = Single Sided - Bezel Mounting Style = Through Bezel Electrical Characteristics: - Data Signal Rate (Gb/s) = Up to 100 Termination Features: - Termination Method to PC Board = Through Hole - Press Fit Dimensions: - Tail Length (mm [in]) = 2.7 [0.1063] - PCB Thickness, Recommended (mm [in]) = 1.57 [0.062] - Length (X-Axis) (mm [in]) = 73.53 [2.895] - Width (Z-Axis) (mm [in]) = 40.45 [1.592] - Profile Height (Y-Axis) (mm [in]) = 27.10 [1.067] Contact Features: Contact Plating, Mating Area, Material = Gold - Tail Plating Material = Gold - Contact Base Material = Copper Alloy - Contact Plating, Mating Area, Thickness (µm [µin]) = 0.76 [29.92] - Underplate Material = Nickel Silver Alloy	Housing Features: - Connector Style = Receptacle Cage Type = Stacked Configuration Features: - Port Configuration = 2x2 - Lightpipe = Without - EMI Containment = EMI Springs Industry Standards: RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance Lead Free Solder Processes = Not reviewed for lead free solder process Conditions for Usage: - Applies To = Printed Circuit Board Operation/Application: Application = zQSFP+ - Heat Sink Application = No Other: - Brand = TE Connectivity

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

