



Part Number : [1300940529](#)
Product Description : Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 4.75-6.35mm (.187-.250"), Approximate Break Strength 136.08kg (300 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 36680



Documents & Resources

Drawings

[1300940529_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 4.75-6.35mm (.187-.250"), Approximate Break Strength 136.08kg (300 lbs)
Product Name	Fiber Optic
Type	Support Grip
UPC	78678836680

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	136.08kg (300 lbs)
Bale Length	0.076m (3.00")
Body Style	Straight
Cable Diameter	4.75-6.35mm (.187-.250")
Color - Grommet	Orange
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.043m (1.70")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 11, 2025