



Honeywell Scanning & Mobility



Vuquest 3310g

Honeywell's Vuquest 3310g compact area-imaging scanner offers aggressive scanning of all 1D, PDF and 2D bar codes in a lightweight, durable and portable form factor. The scanner's sleek and elegant design also blends seamlessly in retail environments.

Zoom

Features & Benefits

Accessories

Documents

Images

Software

Links

Vuquest 3310g Accessories

Power
46-00525 STD Power Supply: NA plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00526 STD Power Supply: EU plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00870 STD Power Supply: UK plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00528 STD Power Supply: AU plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00529 STD Power Supply: CN plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz

Cables
52-52557-3-FR Cable: RS232, black, DB9, 5V, 2.9m (9.5') straight
52-52558-N-3-FR Cable: KBW, black, PS2, 5V, 2.9m (9.5') straight
52-52559-N-3-FR Cable: USB, black, Type A, 5V, 2.9m (9.5') straight
52-52561-3-FR Cable: USB, black, Type A, 5V, 2.9m (9.5') straight, External IO
52-52562-3-FR Cable: RS232black, DB9, 5V, 2.9m (9.5') straight, External IO

Stand/Holder
46-01210: Vuquest presentation-tray stand