



Part Number : 358421301

Series Number : 35842

Product Category : Sockets

Product Description : PT Bulb Socket, Double Housing Assembly, Type A, Sealed, Black

Status : Obsolete

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Sockets
Series	35842

Description	PT Bulb Socket, Double Housing Assembly, Type A, Sealed, Black
Comments	A-Type
Component Type	Socket
Product Family	Automotive Bulb Sockets
Product Name	Bulb Socket
UPC	756054202869

Electrical

Current - Maximum per Contact	5.0A, 7.0A
Voltage - Maximum	12V

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	30
Entry Angle	Vertical
Keying to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Resin	Nylon
Net Weight	11.200/g
Packaging Type	Bag
PCB Locator	No
PCB Retention	N/A
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

This document was generated on Jul 30, 2024