

**Part Number :** 191640050

**Product Description :** Perma-Seal Female Quick Disconnect Receptacle for 16-14 AWG Wire, Tab Size 6.35 x 0.81mm, Carton



**Series Number :** 19164

**Status :** Active

**Product Category :** Quick Disconnects

**Engineering Number :** SBB-9263

---

## Documents & Resources

### Drawings

191640050\_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-013-001.pdf

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## **Part Details**

### **General**

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Female Quick Disconnect Receptacle for 16-14 AWG Wire, Tab Size 6.35 x 0.81mm, Carton
Product Name	Perma-Seal
Type	Standard Quick Disconnect
UPC	800753113350

### **Agency**

CSA	LR18689
UL	E79133

### **Electrical**

Voltage - Maximum	600V
-------------------	------

### **Physical**

Barrel Type	Closed
Color - Resin	Blue
Gender	Female
Glow-Wire Capable	No
Insulated	Fully

Insulation	NiAc
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.343/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	4.32mm max.
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.00-2.50

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool	<a href="#"><u>640014500</u></a>
PremiumGrade Hand Crimp Tool for Industrial Terminals 22-14 AWG (see ATS)	<a href="#"><u>640014700</u></a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#"><u>640054500</u></a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#"><u>640054700</u></a>
ServiceGrade Hand Crimp Tool - Ratchet	<a href="#"><u>640160042</u></a>

---

This document was generated on Sep 24, 2025