



Part Number : [1301470035](#)
Product Description : Watertite Extreme
Receptacle Connector, 3 Pole/3 Wire, Non-
NEMA, 250V, Cord Grip Body Size F3
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Number : 27W08



Documents & Resources

- Drawings**
[Drawing 1301470035_sd.pdf](#)
- 3D Models and Design Files**
[3D Model 1301470035_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle Connector, 3 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F3
IP Rating	IP67
NEMA Configuration	Non-NEMA
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871390

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	N/A
Flange	No
Flip Lid	No

Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/3-wire
Receptacle Type	Single

This document was generated on Sep 26, 2024