
Data sheet

SH 2 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Busbar support, medium yellow, 130 °C, Width: 40 mm, V-0, KrG, when screwed in
Order No.	0641720000
Type	SH 2 S
GTIN (EAN)	4008190166304
Qty.	10 items

Downloaded from Arrow.com.

Data sheet

SH 2 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	35.5 mm	Depth (inches)	1.3976 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	40 mm	Width (inches)	1.5748 inch
Net weight	26.9 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	KrG	Surface finish	all others
Colour	medium yellow	UL 94 flammability rating	V-0

System specifications

Version	For the mounting rails

Additional technical data

Type of mounting	when screwed in

Conductors for clamping (rated connection)

Type of connection	Miscellaneous

General

Number of poles	1	Surface finish	all others

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		

Downloaded from Arrow.com.