



Languages ▼

Registered users

Login

Password

GO

Forgot password?

Register Now

search: by P/N or text

GO

PRODUCTS

CONNECTION TYPE

PRODUCT MICROSITES

APPLICATIONS

Home

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=YO04015000J0G* > YO04015000J0G

YO04015000J0G

YO04015000J0G -

Terminal Blocks :

Rising clamp
system, horizontal
wire-inlet, 3.5 mm
pitch, solid block, 4
position

Specifications

Download document

General Physical Electrical Dimensional Approvals / Certifications Mounting

General

Packaging	Box
Product Type	Rising Clamp System
Number of Positions	4
Series Number	YO

Physical

Soldering temperature (celcius)	260 +/- 5 Celcius (5 sec)
Color (Housing)	Green
Conductor entry angle	0°
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Brass
Terminal plating	Tin
Screw material	Steel
Screw plating	Zinc
Clamp material	Brass
Clamp plating	Nickle
Connection Type	Screw connection
Temperature (Operating - range)	-40 to 115 Celcius
Torque	1.7 Lb-in

Electrical

Withstanding Voltage	1.6 kV
Current rating	10 A
Voltage rating	300 V

Dimensional

Strip length (Wire)	5 to 6 mm
Solid wire size (AWG)	16 to 24
Solid wire size (mm2)	0.2 to 1.5
Stranded wire size (AWG)	16 to 24
Stranded wire size (mm2)	0.2 to 1.5
Pitch	3.5 mm

© FCI 2014 All Rights Reserved | Privacy Policy | Terms of Use