Specification Sheet

Part Number: T30RSF0M4



All-in-one bundling and fastening solution reduces costs and assembly time.

The arrowhead design of these ties offers a low insertion force and a high extraction force.

High-spec materials and superior design deliver versatility, performance and value.

1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg

Article Number	126-00702
Type	T30RSF(U)
Color	Black (BK)
Quantity Per	pack
Product Description	One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.
Short Description	1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg

Downloaded from Arrow.com.

Global Part Name	T30RSF(U)-PA66HS-BK
Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	6.3
Length L (Metric)	160.02
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.22
Bundle Diameter Max (Metric)	31.0

Downloaded from Arrow.com.

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	.20
Height H (Metric)	5.70
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.09
Panel Thickness Min (Metric)	0.9
Panel Thickness Max (Metric)	2.4
Mounting Hole Diameter D (Imperial)	0.19 - 0.22 "
Mounting Hole Diameter D (Metric)	4.7 - 5.6 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Downloaded from Arrow.com.

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.