



- NOTES:
1. PARTS TO BE BULK PACKED.
 2. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTE WITH A TOLERANCE. DIMENSIONS IN BRACKET [] ARE METRIC.




ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING



ASSEMBLED VIEW SHOWN
WITH WINGED
COUPLING RING


KIT PART NO.	GROMMET SIZE TO FIT CABLE O.D.	KIT P/N	NO/ OF CONTACTS
W3280-1XSG-318(W)	0.18 - 0.20 [4.6-5.1mm]	W3280-10SG-3XX	(10) - #20
W3280-1XSG-321(W)	0.21 - 0.23 [5.3-5.8mm]	W3280-11SG-3XX	(11) - #20
W3280-1XSG-324(W)	0.24 - 0.27 [6.1-6.8mm]	W3280-12SG-3XX	(12) - #20
W3280-1XSG-328(W)	0.28 - 0.29 [7.1-7.4mm]	W3280-10SG-3XX(W)	(10) - #20
W3280-1XSG-330(W)	0.30 - 0.32 [7.6-8.1mm]	W3280-11SG-3XX(W)	(11) - #20
W3280-1XSG-3DC(W)	0.12-0.17-0.24 [3.0-4.3-6.1mm]	W3280-12SG-3XX(W)	(12) - #20
(WING COUPLING RING OPTION)		ADD W SUFFIX FOR WINGED COUPLING RING OPTION	
NO. OF CONTACTS		W3280-1XSG-3XX(W)	

GROMMET SIZE
SEE P/N LIST
NO. OF CONTACTS




FACE VIEW
W3280-12SG-3XX(W)



O-RING
MAT'L: RUBBER,
BLACK




CABLE INSERT, FEMALE
MAT'L: UV THERMOPLASTIC,
BLACK




#20 SOCKET CONTACTS
CRIMP,
GOLD PLATED




GROMMET,
MAT'L: RUBBER,
BLACK
FOR CABLE O.D.
SEE TABLE




SLEEVE
MAT'L: THERMOPLASTIC,
BLACK




BACKSHELL
MAT'L: UV THERMOPLASTIC,
BLACK




WIRE VIEW
12-position



FACE VIEW
W3280-10SG-3XX(W)




FACE VIEW
W3280-11SG-3XX(W)




COUPLING RING
MAT'L: UV THERMOPLASTIC,
BLACK


COUPLING RING, WINGED (OPTIONAL)
MAT'L: UV THERMOPLASTIC,
BLACK



CONTACT
INSERTION VIEW



ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING



ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY: _____	DATE: _____

A	PAK	08/15/19	DRAWING CREATED & RELEASED PER DOR 10-2523JS-1	
REV.	INIT.	DATE	DESCRIPTION	
	PAK	10/01/14	ORIG. DRAWN BY: DATE: 10/01/14	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY: _____	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY: _____	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			TITLE: CABLE CONNECTOR KIT #20 SOCKET CONTACTS (CRIMP) MULTI-CON-X, E-KEY, WEATHER RESISTANT STANDARD PRODUCT	
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE: NTS	SHEET: 1 OF 1
FILE: W3280-1XSG-3XX			DIRECTORY: SLW	PART NUMBER: W3280-1XSG-3XX(W)
				REV: A