

Sales Outline Drawing
Revision B

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz)	2900 ± 500
Operating Voltage (Vdc)	3 ~ 28
Rated Voltage (Vdc)	12
Current Consumption (mA/max)	8 at Rated Voltage
Sound Pressure Level (dB/min)	90 at 30cm at Rated voltage
Tone/Pulse Rate (Hz0)	Constant
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Condition by wave solder (°C)	260 ± 5 / within 5 sec
Condition by hand solder (°C)	350 ± 20 / within 5 sec
Housing	ABS 777D plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	12.2
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

