

Specifications

Photo is representative

Eaton 5NCLPT-2E

Eaton Bussmann series medium auxiliary fuse, VT fuse-link, medium voltage, 1 A, AC 5.5 kV, 142 x 25.4 mm, back-up, BS, IEC, US, 1E, Protect of auxiliary trans, 1 A, 1E, 50K A Breaking Cap, Inst Air, E, British Standard, Class back-up

General specifications

PRODUCT NAME	Eaton Bussmann series medium auxiliary fuse
CATALOG NUMBER	5NCLPT-2E
UPC	051712697538
EAN	5027590093989
PRODUCT LENGTH/DEPTH	5.63 in
PRODUCT HEIGHT	0.81 in
PRODUCT WIDTH	0.81 in
PRODUCT WEIGHT	1.45 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	IEEE Std. C37.41
CATALOG NOTES	Consult factory for mountings.
GLOBAL CATALOG	5NCLPT-2E
PRODUCT TYPE	Medium voltage auxiliary fuse

Product specifications

AMPERAGE RATING	2 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	143 x 20.6 mm 0.81" X 5.63"
BREAKING CAPACITY	63 kA
PRODUCT APPLICATION	Auxiliary transformer protection
RELEASE CHARACTERISTIC	E
STANDARD	ANSI
VOLTAGE TYPE	AC
CLASS	Class E
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical
FUSE DIAMETER	0.81 in
INTERRUPT RATING	63 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	143 x 20.6 mm 0.81" X 5.63"
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	5.5 kV
TYPE	NCLPT
SPECIAL FEATURES	Non-Indicating
FUSE TYPE	NCLP

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES

[eaton-bussmann-series-product-range-overview-brochure-br134002en-en-us.pdf](#)

[eaton-bussmann-circuit-protection-brochures-en.pdf](#)

CATALOGS

[Current Limiting Fuses, Volume 14, Tab 3](#)



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

