

WML 7,5 (25X13)R

Order No.: 0800075

The figure shows the WML 5 (25x10)R version



<http://catalog.phoenixcontact.net/phoenix/treeViewClick.do?UID=0800075>

Cable marker label, Roll, white, Unlabeled, Can be labeled with:
Thermomark R, Thermomark X, Thermomark S, Mounting type:
Adhesive, Cable diameter: ≤ 7.5 mm, Lettering field: 25 x 13 mm

Commercial data

EAN	4 046356 562089
sales group	B123
Pack	1 Pcs.
Customs tariff	39191019
Gross weight in pieces	0.73075 KG
Net weight per piece	0.73075 KG
Catalog page information	Page 160 (CL2-2011)

Product notes

WEEE/RoHS-compliant since:
01/27/2010



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Length (b)	36.5 mm
Width (a)	25.4 mm
Color	white
Base element material	Vinyl film
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Ambient temperature (operation)	-50 °C ... 110 °C
Components	Silicone-free
Material	PVC
Number of individual labels	2100
Number of individual labels per row	3
RoHS compliant	Yes
Halogen-free	Yes
Silicone-free	Yes
Cadmium-free	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5145313 THERMOMARK S1
	5146257 THERMOMARK S1.1
	5145274 THERMOMARK X1.1
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2006-02 + A1:2009-07
Duration of test	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Burning behaviour	self-extinguishing
Foil strength	0.06 mm

Certificates / Approvals

Certification
Certifications applied for:
Certification Ex:

Accessories

Item	Designation	Description
------	-------------	-------------

General

5145384	THERMOMARK-RIBBON 110	Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black
---------	-----------------------	--

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>



© 2012 Phoenix Contact
Technical modifications reserved;