

Full text search...

GO

Productfinder...

- General information
- Rocker switches
- Pushbutton switches
- Toggle switches
- Slide switches
- Rotary switches
- Foot switches
- Tact and key switches
- Snap-action switches
- Micro-signal switches
- Sensors
- Catalog request / download

- Login
- www.marquardt.com
- Download
- Sales international
- Partner access

SERIES 1065- MICRO-SIGNAL SWITCHES TO 100 MA 30 V DC

Previous

Product 5 of 16

Next

Technical data

Product number	1065.2563		
Switching function	Changeover switch (SPDT momentary)		
Number of poles	1-pole		
connections	PCB terminal		
Mechanical life endurance	200E3		
Rating IEC	100 mA 30 V DC 2E5		
Contact resistance (new condition)	< 500 (1 A 12 V DC) mOhm		
Insulation resistance (new condition)	1 000 MOhm		
Protection type	Connection	IP 00	
Temperature	Connection side min.	-40 °C	
	Connection side max.	85 °C	
Actuators and additional actuators	POM, standard actuator, silicone rubber		
Housing description	PBTP, pin both sides 5 long		
Connection surface	external connection	tinned	
Contact material	AuCo		
Shock resistance	50 g		
Miscellaneous	terminal side sealed		
Operating force	1 ±0.4 N		
Free position (FP) max.	10.15 mm		
Permissible total travel position	6.85 mm		
Operating position NCC	13.8 ±0.3 mm		
Operating position NOC	13.3 ±0.3 mm		
Stock version			

Back

To product table

To request

Product image / drawing



Similar to original product



Further information

Drawing