C2G

Discontinued - 100ft (30.5m) Cat5e Snagless Unshielded (UTP) Ethernet Network Patch Cable - Blue

Part No. 10289



For voice/data/video distribution, this cable will handle bandwidth-intensive applications. Meets all TIA/ANSI Cat5e standards and the stringent TAA compliance requirements for anyone who needs to procure products exclusively manufactured in countries on the Trade Agreement Act list.

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point.

Constructed from high quality cable and a shortened body plug, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Designed for network adapters, hubs, switches, routers, HDBaseT applications and more
- Supports 1 Gigabit networks up to 328ft for fast data transmission and maximum performance
- Meets all Cat5e TIA/EIA requirements for supporting a wide variety of applications
- Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk
- Snagless connector design for high density environments and protecting the RJ-45 connector's lock

Specifications

General Info

Product Line	C2G	Replaced by Part Number	10322
Color	Blue	UPC Number	757120102892
Country Of Origin	Taiwan, Province Of China	Application Sector	Commercial, Industrial, Residential
Type	Cable		

Dimensions

Cable Length	100 ft

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat5e
Wire Gauge	24 AWG	Shielded/Unshielded Cable	Unshielded
Shield Type	UTP	Cable Type	Ethernet Patch Cable
Jacket Rating	Standard / Non-Rated	Cable Diameter	5.3 mm

Downloaded from Arrow.com.

Connector Type	Booted, Snagless	Indoor/Outdoor	Indoor
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male

Downloaded from Arrow.com.