



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X3MYL

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Yellow, 3m.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Conductor Gauge (AWG)	28
Performance Level	Category 6A
Connector 2 Type	RJ45 8(8)
Connector 1 Type	RJ45 8(8)
Overall Length (ft.)	9.84
Overall Length (m)	3
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Flammability Rating	CM, LSZH-1 (60332-1)
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Cable Color	Yellow
Length (ft.)	9.84
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.19
Nominal Cable Outside Diameter (mm)	4.7
UL5A Listed	No
Application	Shielded
Cable Length (ft.)	9.84
Cable Length (m)	3

Cable Type	F/UTP
Conductor Material	Copper
Maximum Installation Temperature (°C)	70
Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	70
Minimum Installation Temperature (°F)	-40
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)