












Max. Temperature: 260° during 10 seconds.

0955 469 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)		
0955 469 3812 741	1	4-40 UNC				
0955 469 6811 741	2	M3				
0955 469 6812 741	2	4-40 UNC				
0955 469 7811 741	3	M3				
0955 469 7812 741	3	4-40 UNC				
Part number	PL	Nut	Index designation			
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances	
					D-Sub SMT, 37 poles Male, Straight with nuts and ground pins	
					D-Sub SMT, 37 poles Male, Straight with nuts and ground pins	
			Zhuhai HARTING Limited			TB 09 55 469 x81x
EC04070	17-Nov-11	Johnson.S				
Mod.	Dat.	Name	Sub.			Page 1/2



See TB 09 55 469 x81x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 469 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 469 3812 741	1	4-40 UNC		
0955 469 6811 741	2	M3		
0955 469 6812 741	2	4-40 UNC		
0955 469 7811 741	3	M3		
0955 469 7812 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
				Dat.	Name	Scale	D-Sub SMT, 37 poles Male, Straight with nuts and ground pins	
			Detail.	25-Oct-11	Johnson.S			
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
			Zhuhai HARTING Limited 			TB 09 55 469 x81x		Page 2/2
EC04070	17-Nov-11	Johnson.S				Sub.		
Mod.	Dat.	Name						