

## Serial DB9 Serial Extension Cable, Straight Through (DB9 M/F), 6 ft. (1.83 m)

MODEL NUMBER: **P520-006**

### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

### Package Includes

- 6-ft. (1.83 m) RS-232 Serial Extension DB9F to DB9M

### Description

This extends an RS-232 Serial cable by an additional six feet (1.8 meters). Foil-shielding construction provides maximum EMI/RFI protection. The DB9 female and DB9 male connectors are molded with built-in strain relief to ensure that the cable lasts a long time.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- DB9 (male) to DB9 (female)

## Specifications

OVERVIEW	
UPC Code	037332012388
Technology	Serial
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DB9 (MALE)
Side B - Connector 1	DB9 (FEMALE)
PHYSICAL	
Color	Gray
Cable Jacket Color	Gray
Cable Length (ft.)	6



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0-90% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.