



1 - 207596 - 0



Active

Not ELV or RoHS Compliant

Product Highlights:

- ? Sealed
? Seal Type = Environmental
? Shell Size = 2 Inserts
? Shell Configuration = Plug
? Contact Arrangement (Module A) =
106

[View all Features](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- [? PLUG CONNECTOR INSTALLATION \(WITH CENTER MALE JACKSCREW\) \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

List all Documents

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Sealed = Yes
- ? Shell Size = 2 Inserts
- ? Shell Finish = Cadmium plated per QQ -P-416
with yellow chromate conversion.
- ? Thread Size = 10 -24 Double Lead Thread
- ? Comment = Coaxial contacts must be ordered
separately

Mechanical Attachment:

- ? Keying = 01
- ? Hardware Type = Center Male Jackscrew

Electrical Characteristics:

- ? Shell Configuration = Plug
- ? Signal Contacts = With
- ? Shell Mounting Modification = 50
- ? Custom Order Code = 200

Termination Related Features:

- ? Seal Type = Environmental

Contact Related Features:

- ? Contact Type (Module A) = Socket
- ? Contact Type (Module B) = Pin

Configuration Related Features:

- ? Contact Arrangement (Module A) = 106
- ? Contact Arrangement (Module B) = 32C2

Industry Standards:

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = Not ELV/RoHS compliant
- ? Lead Free Solder Processes = Not relevant for lead free process

Other:

- ? Brand = AMP