
Product Line

- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
  - Accessory
  - Middle Size
  - Mini Size
  - Large Size
  - Standard Size
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





AU-08BFFB-QL8AP0

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



X-Lok, Mini Size, Plasti...
AB-AU08ML-AUFL-...
-20°C ~ +80°C



X-Lok, Mini Size, Plasti...
AB-AU08ML-AUFL-...
-20°C ~ +80°C



X-Lok, Mini Size, Plasti...
AB-AU08ML-AUFL-...
-20°C ~ +80°C



X-Lok, Mini Size, Plasti...
AB-AU08ML-AUFL-...
-20°C ~ +80°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current: **2A**	Connector Type: **Field Installable**
Shielded: **Plastic, Non-shielded**	No. of Contacts: **08**
Connector Gender: **Female**	Backshell: **Straight**
Mating Style: **Push Lock**	IP Rating: **IPX8**
Assembly Style: **Screw-in**	

More Options

People Also Bought

Downloaded from Arrow.com.