

NOTES:



- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE  
HARTING P/N

WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
79	AWG 30	79
80	AWG 30	80

HARTING P/N	Cable length(L)
3315 243 010 0123	100 ± 3
3315 243 020 0123	200 ± 5
3315 243 050 0123	500 ± 10

		All Dimensions in mm Original Size DIN A3		Scale 1.5:1		Free size tol. \\		Ref. \		
								Sub. \		
		All rights reserved		Created by ZHENGL		Inspected by WANGE		Standardisation CHENJU		
		Department HCS - CN						Date 2018-10-12		
								State Final Release		
HARTING Customised Solutions  D-32339 Espelkamp		Title Har-Flex 80 Pole,Dul-end,With SR,L=XXMM							Doc-Key / ECM-Nr. 100586986/UGD/000/A 500000141226	
		Type TB		Number 33150024					Rev. A	
									Page 1/1	