

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	02NOV2016	KZ	RS

ASSEMBLED 2061926-X

SCALE 1:2



1

Ø 29,2

(102)

2

Ø 21,2

3

"L"

TE Part Number	"L" (mm)	Cable Diameter
2061926-1	500 ±20	4.8±0.2 mm
2061926-2	300 ±20	4.8±0.2 mm

NOTES:

1. THIS FIELD INSTALL KIT SHOULD BE USED WITH RUGGEDIZED CABLE AND RUGGED FAN-OUT CONSTRUCTION
NO 900 MICRON TERMINATIONS TO BE USED.

2. CABLE DIAMETER RANGE: SEE TABLE

3. THE FLAMMABILITY RATING OF THE MATERIAL IS UL94-V0

4. THE MATERIAL IS HALOGEN FREE ACCORDING IEC 60754-2

5. EACH ASSEMBLY IS PACKED IN A PROTECTIVE SLEEVE
- GLAND SEAL AND NUT ARE SEPARATELY SEALED

6. AN INSTRUCTION SHEET IS PACKED WITH EACH FIELD INSTALL KIT

3	FuIIFLEX MINI FIELD INSTALL NUT FOR CABLE GLAND	1
2	FuIIFLEX MINI FIELD INSTALL CABLE GLAND SEAL	1
1	FuIIFLEX MINI FIELD INSTALL CORRUGATED TUBE with COUPLING	1
Item	Description	Qty

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0,5

1 PLC ±0,25

2 PLC ±0,03

3 PLC ±0,005

4 PLC ±0,0010

ANGLES ±1

MATERIAL

-

FINISH

-

DWN R. COOLEN 08APR2015

CHK M. SCHOLTEN 08APR2015

APVD S. BORGAS 08APR2015

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE

TE Connectivity

NAME

FuIIFLEX MINI FIELD INSTALL KIT

SIZE A3

CAGE CODE -

DRAWING NO C-2061926

RESTRICTED TO -

SCALE 4:5

SHEET 1 OF 1

REV A

1470-19 (3/13)

Downloaded from Arrow.com