Data sheet

ZQV 1.5N/R6.4/19 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	TERMSERIES, Cross-connector
Order No.	1391600000
Type	ZQV 1.5N/R6.4/19 SW
GTIN (EAN)	4050118191806
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2021-06-30T00:00:00+02:00
Alternative product	TCC 6.4/51 BK

Downloaded from Arrow.com.

Data sheet

ZQV 1.5N/R6.4/19 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	4.9 mm	Depth (inches)	0.1929 inch
Height	13.1 mm	Height (inches)	0.5157 inch
Width	119 mm	Width (inches)	4.685 inch
Net weight	4.65 g		

Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...60 °C
Operating temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Rated current (UL)	10 A

General data

Version	can be cut to length	Colour	black

Insulation coordination

Rated voltage	250 V

Connection data

Pitch in mm (P)	6.40 mm

Classifications

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		

Downloaded from Arrow.com.


ZQV 1.5N/R6.4/19 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing



Downloaded from Arrow.com.