




DO NOT SCALE
DIMENSIONS IN mm

METRIC




NOTES:

- △1 BARREL TERMINALS WILL ACCEPT ONE OR TWO WIRES OF THE SAME SIZE PER TERMINAL.
WIRE SIZE FOR SOLID AND STRANDED WIRES:
0,12 mm² (26 AWG)–0,35 mm² (22 AWG).
MAXIMUM INSULATION DIA. 1,2 mm.
- △2 STUFFER CAP IS SHIPPED NOT ASSEMBLED.
- △3 MATERIALS: STUFFER CAP – A.B.S. UL 94HB
BARREL TERMINALS – PHOS.BRONZE, PRE-TINPLATED.
CONTACTS – PHOS.BRONZE, PLATED 1,25
SELECTIVE GOLD OVER 1,25
HOUSING – PBT, UL 94HB
- △4 FOR 216000-2 DIMENSION 15,2 IS 14,6 ,
CORRESPONDING WITH THE MARKED DASH LINES
- △5 NO STUFFER CAP INCLUDED



△2
STUFFER CAP
[1 PC PER KIT]




SUGGESTED PANEL CUTOUT DIMENSIONS

SCALE 2 : 1


X-216000-1

X-216000-2, -3 AND -5



CUTOUT FOR
BACK PANEL
MOUNTING

CUTOUT FOR
FRONT PANEL
MOUNTING



CUTOUT FOR
BACK PANEL
MOUNTING

CUTOUT FOR
FRONT PANEL
MOUNTING

PANEL THICKNESS: 1,6 mm NOMINAL

TOLERANCE: ±0,15 UNLESS SPECIFIED OTHERWISE

OBSOLETE

500 PCS. IN A BOX	SEE NOTE △3	HOUSING COLOR: BLACK SEE NOTE △3	△5 9-216000-3
			216000-2
			216000-1
PACKAGING	FINISH	MATERIAL	PARTNUMBER
CUSTOMER DRAWING			FOR REFERENCE ONLY WILL NOT BE UPDATED
THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION			
NAME			
TOOLLESS MODULAR JACK KIT			
6 POS., FOR DISCRETE WIRES			
R2	REVISED PER ECO-11-005294	RK	HMR 05APR11
LTR.	REVISION RECORD	DR.	CHK. DATE
DR.: J.V.LIEMPT	CHK.: W.BRUMMANS	APP.: L. v. SOEST	DWG.No.
DATE: 21 JAN 91	DATE:	DATE: 12 OCT 94	C-216000
		REV.LTR.	SHEET
		R2	1 OF 1
		A2	

11

10

9

8

7

6

5

4

3

2

1