

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0082286161

Status:

Active

Description:

2.54mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded, Topcoat, 16 Circuits, Reel 30.48m Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	7767
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800755002966
Physical	
Cable Length	30.48m
Circuits (Loaded)	16
Insulation	PVC
Net Weight	1499.936/g
Packaging Type	Reel
Pitch - Termination Interface	2.54mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	28
Wire/Cable Type	(7x36) Stranded, Topcoat
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	300V
Material Info	
Engineering Number	7767-16-100B
Reference - Drawing Numbers	
Sales Drawing	SD-7767-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7767 Series

Use With

70400 C-Grid SL IDT Connector Assembly.

70475 SL IDT Connector Assembly. 7720

KK IDT Double Cantilever Contact

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION