

Specification Sheet

Part Number: 133-04509

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications.

Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength.

HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Article Number	133-04509
Type	CCFT6.5LG-TS5
Color	Light Gray (LTGY)
Quantity Per	bag
Product Description	Connector clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, they can be attached to a hole, edge, stud or even another harness assembly.
Short Description	Connector Clip w/Round Fir Tree, 6.1 - 6.9 mm Hole Dia, PA66HIRHS, Light Gray, 4,000/ctn

Global Part Name	CCFT6.5LG-TS5-PA66HIRHS-GY
------------------	----------------------------

Length L (Imperial)	1.13
---------------------	------

Length L (Metric)	28.76
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Width W (Imperial)	0.52
--------------------	------

Width W (Metric)	13.2
------------------	------

Height H (Imperial)	0.82
---------------------	------

Height H (Metric)	20.9
-------------------	------

Panel Thickness Min (Imperial)	0.06
--------------------------------	------

Panel Thickness Max (Imperial)	0.16
--------------------------------	------

Panel Thickness Min (Metric)	1.5
------------------------------	-----

Panel Thickness Max (Metric)	4.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.27
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.24
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.9
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

