

AR8645

Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 10"W, Double-Sided with Doors



Product availability: Stock - Normally stocked in distribution facility



Overview

Presentation	This 10" wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a double-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.
Lead time	Usually in Stock

Main

Provided equipment	Doors Installation guide Mounting Hardware 3 x Midspan brackets
--------------------	--

Physical

Color	Black
Height	84.02 In (213.4 cm)
Width	9.96 In (25.3 cm)
Depth	25.98 In (66 cm)
Net Weight	75.0 Lb(US) (34 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	UL Listed
------------------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

### Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1
GTIN	731304291596
Returnability	No
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.98 In (40.6 cm)
Package 1 Width	90.04 In (228.7 cm)
Package 1 Length	32.52 In (82.6 cm)
Package 1 Weight	95.02 Lb(US) (43.1 kg)

### Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	Yes

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**