

**Product Line**

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >**
  - Accessory
  - PWC
  - PWCU
  - PWE
  - PWF
  - PWG
  - PWH
  - PWL
  - PWM**
  - PWMU
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



**PWM-02BFMB-TL7001**

Operating Temperature: -40°C ~ +105°C  
 Transmission Speed: N/A  
 Shielded: Plastic, Non-shielded  
 Jacket Material: N/A  
 Certificate: UL1977

You must login first for view the price

Quantity

[Check Stock](#)

[Add to Cart](#)

[Inquiry](#)



Can't find? [Customize your part](#)

Specifications	Download / CAD
Nominal Current <b>50A</b>	Connector Type <b>Field Installable</b>
Shielded <b>Plastic, Non-shielded</b>	No. of Contacts <b>02</b>
Connector Gender <b>Female</b>	Backshell <b>Straight</b>
Mating Style <b>3 Points Lock</b>	IP Rating <b>IP67</b>
Assembly Style <b>Screw-in</b>	
<a href="#">More Options</a>	

**People Also Bought**

-   
[PWM-02BFMB-TL7001](#)
-   
[AB-DD18FL-DDHL-...](#)
-   
[DD-12RFMS-RCBCAO](#)
-   
[BBD-068FMM-...](#)
-   
[CD-04RFMC-RS7B10](#)