Part Number : 1301250002
Product Description : Wire Rope Festoon Car Round, 31.75mm (1.250") Cable Height - Maximum
Series Number : 130125
Status : Active
Product Category : Festoons
Engineering Part Number : 5131



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:
EU RoHS	Not Relevant

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Festoons
Series	130125
Description	Wire Rope Festoon Car Round, 31.75mm (1.250") Cable Height - Maximum
Component Type	Car - Intermediate
Product Name	Aero-Motive
Type	Wire Rope
UPC	78678863144

Physical

Cable Height - Maximum	31.75mm (1.250")
Combined Cable Weight-Max./Car	4.08kg (9.0 lb)
Depth	51.40mm (2.024")
Duty	Light
Height	137.92mm (5.430")
Length	86.25mm (3.400")
Material - Metal	N/A
Material - Resin	Nylon
Material - Wheel	Steel - Sealed Ball Bearing
Net Weight	573.790/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	N/A
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Round

Downloaded from Arrow.com.