TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

MAGNET WIRE TERMINALS



✔ Active

TE CONNECTIVITY (TE)

MAG-MATE CONTACT WITH SOLDER PIN

Magnet Wire Terminals & Splices | MAG-MATE

1534686-7
TE Internal Number: 1534686-7

EU RoHS Compliant
EU ELV Compliant

Terminal Type Solder Post

Magnet Wire Size (mm) .4 – .63

Magnet Wire Size (AWG) 26 – 23

Material Thickness (in) .0126

Plating Material Nickel

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

MAG-MATE Kontakt Mit Loetpin Baugroesse .300 Mod.
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Downloaded from Arrow.com.

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

Magnet Wire Terminals & Splices

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Body Features

Plating Material Nickel

Contact Features

Terminal Type Solder Post

Dimensions

Magnet Wire Size (mm) .4 – .63
Magnet Wire Size (AWG) 26 – 23
Material Thickness (in) .0126

Packaging Features

Packaging Method Reel, Reel/Carton

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.