
Part Number : 15311032
Product Description : 4.80mm Pitch Wire-to-Wire Receptacle Housing, 3 Circuits
Series Number : 5025
Status : Active
Product Category : Connector Housings
Engineering Part Number : 5025-03R1



Documents and Resources

Drawings

015311032_sd.pdf

SPK-5025-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-5025-001-001.pdf

PS-5025-002-001.pdf

PS-5025-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	5025
Description	4.80mm Pitch Wire-to-Wire Receptacle Housing, 3 Circuits
Application	Wire-to-Wire
Product Name	N/A
UPC	800753622111

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Net Weight	1550.800/mg
Number of Rows	1
Packaging Type	Bag

Downloaded from Arrow.com.

Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
4.80mm Pitch Wire-to-Wire Plug Housing, 3 Circuits	15311031
4.80mm Pitch Wire-to-Wire Plug Housing, 3 Circuits	15311033

Use with Part(s)

Description	Part Number
4.80mm Pitch Female Crimp Terminal	5005

Downloaded from Arrow.com.