



YAV25L16G1

by Burndy
Catalog ID: YAV25L16G1

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Hole, AN-1/0 Flex,7/16" Stud, Short Barrel, Electro-Tin Plated

Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	43
Feature - Barrel Style	- Chamfered - Skived
Feature - Barrel Type	Standard
Material	Copper
Material Composition	- DLP Copper - Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810372388

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.45 in
Dimension - D inch	0.90 in
Dimension - Hole Size mm	12 mm
Dimension - Length Overall inch	2.09 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.83 in
Dimension - Stud Size inch	7/16
Dimension - Z inch	0.46 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 0
--------------------------------------	------

Conductor Type	• CU C Solid-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)