molex
one company › a world of innovation

Part Number: 87858-2050

2mm SR 20P Hdr Hor SMT w Peg Breakaway



Series image - Reference only

Status: Active
Series: 87858
Category: Molex Parts

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant
China RoHS:
REACH SVHC:
Low-Halogen Status: Not Reviewed

Part Detail

General	
Status	**Active**
Category	Molex Parts
Series	87858
UPC	800756898643
Physical	
Net Weight	1.449/g
Solder Process Data	
Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260
Material Info	

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Downloaded from Arrow.com.