

7014PA Product Details



7014PA (1423161-4)

TE Part Number: 1423161-4

✔ [Active](#)

[Add to Part List](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 7000 Electropneumatic Timing Series
- Time Delay Relay
- Input Voltage = 125 VDC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 10A @ 240 VAC

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [None Available](#)

Catalog Pages/Data Sheets:

- [None Available](#)

Product Specifications:

- [None Available](#)

Application Specifications:

- [None Available](#)

Instruction Sheets:

- [7000 Series 4-Pole Timing Relay](#) (PDF, English)

CAD Files:

- [None Available](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Time Delay Relay
- Termination Type = Screw Terminal

Electrical Characteristics:

- Input Voltage (VDC) = 125
- Contact Rating = 10A @ 240 VAC

Body Related Features:

- [Series](#) = 7000 Electropneumatic Timing

Contact Related Features:

- Mounting Options = Panel Mount
- Mode of Operation = On-Delay
- Delay Time = 0.2 seconds to 2 seconds
- Type of Control = Knob
- Repeatability, Max. = ± 10%
- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

Configuration Related Features:

- [Contact Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = -30 – +75

Other:

- Brand = Agastat