



Manage this device with
Digi Remote Manager

DIGI CORE PLUG-IN LTE MODEM

Modular LTE connectivity with Carrier Smart Select and dual SIM support across major carriers for optimal mobile network access

Stay connected with Digi CORE® plug-in LTE modems for LTE, LTE-Advanced and LTE-Advanced Pro connectivity across major cellular networks. The modular design integrates with a range of Digi high-performance routers and infrastructure devices, including Digi EX15, Digi IX20, Digi 6310-DX, Digi 6330-MX, Digi 6350-SR, Digi Connect® IT 4 and Digi AnywhereUSB® Plus.

With Digi CORE plug-in modems, enabled Digi devices can connect to mobile networks using the LTE standard that best suits each use case. Larger locations or data-intensive applications can utilize LTE-Advanced Cat 6, Cat 11 and LTE-Advanced Pro Cat 18 versions of the Digi CORE plug-in modem to take advantage of faster speeds and carrier aggregation.

Meanwhile, applications with less intensive needs can opt for the cost-saving deployment of a standard LTE Cat 4 or Cat 3 connection. Select the router and modem that best fit current and future connectivity needs with the ability to upgrade devices rather than replacing them.

Digi Remote Manager® is a secure cloud-based device management solution that provides remote monitoring and control of Digi enterprise routers and gateways after deployment. It enables easy setup, configuration and support for installations of Digi devices.

FEATURES AND BENEFITS

- Certified with major cellular carriers
- Scalable throughput with multiple module types:
 - LTE-Advanced Cat 6, Cat 11 and LTE-Advanced Pro Cat 18
 - LTE Cat 4 with 3G / 2G fallback on select modules
 - LTE Cat 3 with EVDO fallback (UMTS / HSPA+)
 - LTE Cat M1 / NB1 with 2G fallback (EGPRS)
- Dual SIM slots with automatic or manual swapping
- Carrier Smart Select™ for optimal connectivity
- Readily upgrade to meet changing cellular standards
- Tamper-proof optional locking mechanism
- External SMA connectors for custom antenna runs

RELATED PRODUCTS



Digi EX15



Digi 6310-DX



Digi 6330-MX




Digi IX20



Digi Remote Manager

CORE MODEM DIAGRAM



Digi CORE plug-in LTE modem inserted into a Digi enterprise router.

SPECIFICATIONS		DIGI CORE® PLUG-IN LTE MODEM	
SOFTWARE			
REMOTE MANAGEMENT		Digi Remote Manager®	
PROTOCOLS		USB 2.0 / 3.0 (CM module's interface), UMTS, EVDO, HSPA+, LTE, LTE-A (Note: supported cellular protocols vary by module type)	
SECURITY		Tamper-proof with internal SIM slots and optional locking mechanism	
PHYSICAL			
DIMENSIONS (L x W x H)		102 mm x 51 mm x 15 mm (4.0 in x 2.0 in x 0.6 in)	
WEIGHT		0.156 kg (5.5 oz.)	
ENVIRONMENTAL			
OPERATING TEMPERATURE		Commercial temperature: 0° C to 40° C (32° F to 104° F)	
		Industrial temperature: -40° C to 70° C (-40° F to 158° F)	
STORAGE TEMP AND HUMIDITY		-25° C to 75° C (-13° F to 167° F); 5% to 95% non-condensing	
APPROVALS			
EMISSIONS / IMMUNITY		FCC Part 15, Subpart B, Class A; CE, RCM; CAN ICES-3(B)/NMB-3(B)	
CELLULAR SPECIFICATIONS			
CELLULAR ANTENNA*		(2) Dipole; Frequency: 700-960/1575-2700 hz; Gain: 1-4 dBi	
SIM		(2) SIM card slot (size 2FF), software selectable and hardware switchable	
DIGI CORE PLUG-IN LTE MODEM**			
DIGI CORE 1002-CMM1 (GLOBAL)*		LTE Cat M1 / NB1; LTE Bands: B1, B2, B3, B4, B5, B8, B12, B13, B18, B19, B20, B26, B28; 2G (EGPRS): 850 / 900 / 1800 / 1900 MHz; Transfer rate (max): M1: 300 kbps down, 375 kbps up; NB1: 21 kbps down, 62.5 kbps up; 2G: 296 kbps down, 236 kbps up	
DIGI CORE 1002-CM03 (NORTH AMERICA)		LTE Cat 3; LTE Bands: B2, B4, B5, B13, B17, B25; 3G WCDMA: B1, B2, B4, B5, B8; 3G EVDO: BC0, BC1, BC10; 2G: BC0, BC1, BC10; Transfer rate (max): 100 Mbps down, 50 Mbps up; Commercial temperature	
DIGI CORE 1002-CM04 (NORTH AMERICA)		LTE Cat 4; LTE Bands: B2, B4, B5, B12, B13; 3G: B2, B5; Transfer rate (max): 150 Mbps down, 50 Mbps up; Commercial temperature	
DIGI CORE 1002-CME4 (EMEA)		LTE Cat 4; LTE Bands: B1, B3, B7, B8, B20; 3G: B1, B8; 2G: B3, B8; Transfer rate (max): 150 Mbps down, 50 Mbps up; Commercial temperature	
DIGI CORE 1002-CMF4 (NORTH AMERICA)		LTE Cat 4; LTE Bands: B2, B4, B5, B12, B13, B14, B66, B71; 3G: B2, B4, B5; 2G (EDGE): No support; Transfer rate (max): 150 Mbps down, 50 Mbps up	
DIGI CORE 1002-CMG4 (GLOBAL)		LTE Cat 4; LTE Bands: B1, B2, B3, B4, B5, B7, B8, B12, B13, B18, B19, B20, B25, B26, B28, B39, B40, B41; 3G: B1, B2, B4, B5, B6, B8, B19; 2G EDGE / GPRS: 850 / 900 / 1800 / 1900 MHz; Transfer rate (max): 150 Mbps down, 50 Mbps up; Industrial temperature	
DIGI CORE 1002-CM06 (GLOBAL EXCLUDING AU, NZ, JP AND KR)		LTE-Advanced Cat 6; LTE Bands: B1, B2, B3, B4, B5, B7, B8, B12, B13, B20, B25, B26, B29, B30, B41; 3G WCDMA: B1, B2, B3, B4, B5, B8; Transfer rate (max): 300 Mbps down, 50 Mbps up; Commercial temperature	
DIGI CORE 1002-CM16 (APAC)		LTE-Advanced Cat 6; LTE Bands: B1, B3, B5, B7, B8, B18, B19, B21, B28, B38, B39, B40, B41; 3G WCDMA: B1, B5, B6, B8, B9, B19; 3G TD-SCDMA: B39; Transfer rate (max): 300 Mbps down, 50 Mbps up; Commercial temperature	
DIGI CORE 1003-CM11 (GLOBAL)		LTE-Advanced Cat 11; LTE FDD Bands: B1, B2, B3, B4, B5, B7, B8, B12, B13, B17, B20, B25, B26, B28, B29, B30, B66; LTE TDD: B38, B40, B41; 3G: B1, B2, B4, B5, B8; Transfer rate (max): 600 Mbps down, 75 Mbps up; Commercial temperature	
DIGI CORE 1003-CM18 (GLOBAL)		LTE-Advanced Pro Cat 18; LTE FDD Bands: B1, B2, B3, B4, B5, B7, B8, B12, B13, B17, B20, B25, B26, B29, B30, B66; LTE TDD: B38, B39, B40, B41; 3G: B1, B2, B4, B5, B8; Transfer rate (max): 1.2 Gbps down, 150 Mbps up per module; Commercial temperature	
DIGI CORE 1003-CM18 (NORTH AMERICA)		FirstNet Ready™ LTE-Advanced Pro Cat 18; LTE FDD Bands: B1, B3, B7, B8, B12, B13, B14 - FirstNet®, B20, B25, B26, B28, B29, B30, B32, B48, B66, B71; LTE TDD: B38, B39, B40, B41, B42, B43, B46; Transfer rate (max): 1.2 Gbps down, 150 Mbps up per module; Commercial temperature	
WARRANTY			
PRODUCT WARRANTY		3-year	

* Digi CORE 1002-CMM1 requires only one cellular antenna.

** Transfer rates are network operator dependent.

PRODUCT IMAGES


DIGI CORE® PLUG-IN LTE MODEM DUAL SIM




DIGI CORE PLUG-IN LTE MODEM TOP



DIGI CORE PLUG-IN LTE MODEM FRONT



DIGI CORE PLUG-IN LTE MODEM BACK



DIGI REMOTE MANAGER®



Digi Remote Manager is the technology platform that brings networks to the next level, allowing networks — and the people who manage them — to work smarter. With Digi Remote Manager you can transform a multitude of dispersed IoT devices into a dynamic, intelligent network. Now you can easily deploy, monitor and diagnose thousands of mission-critical devices from a single point of command — on your desktop, tablet or phone. All the while, its software-defined security diligently safeguards your entire Digi ecosystem.

Learn more at www.digi.com/digi-remote-manager

CAPABILITIES

- Activate, monitor and diagnose your mission-critical devices from a single point of command and control — on your desktop or mobile app
- Schedule key operations — including firmware updates and file management — on a single device or on a group of devices, keeping your network functionality up-to-date and maintaining compliance standards
- Manage edge devices out-of-band via console terminal access
- Keep tabs on device health and connectivity across device deployments of any size
- Create detailed reports and enable real-time alerts for specified conditions
- Integrate device data through open APIs to gain deeper insights and control with third-party applications
- Report and alert on performance statistics, including connection history, signal quality, latency, data usage and packet loss

INFRASTRUCTURE

- Hosted in a commercial-grade cloud server environment that meets SOC 1®, SOC 2® and SOC 3® standards
- Superior availability, operating to 99.9% or greater
- Open APIs available to support application development

SECURITY

- More than 175 security controls in place to protect your data
- Member of the Center for Internet Security® (CIS®)
- Enables compliance with security frameworks like ISO27002, HIPAA, NIST and more
- Earned Skyhigh's CloudTrust™ Program highest rating of Enterprise-Ready

PART NUMBERS	DIGI CORE® PLUG-IN LTE MODEM
1002-CMM1-GLB	Digi CORE plug-In LTE modem; LTE / M1 / NB1 / 2G (EGPRS) Visit: https://www.digi.com/resources/certifications for latest certifications
ASB-1002-CM03-GLB	Digi CORE plug-In LTE modem; LTE / HSPA+ / EVDO Cat 3; Cellular certifications: PTCRB, AT&T, Verizon, Sprint, T-Mobile
ASB-1002-CM04-OUS	Digi CORE plug-In LTE modem; LTE / HSPA+ Cat 4; Cellular certifications: PTCRB, AT&T, Verizon, Canada
ASB-1002-CME4-GLB	Digi CORE plug-In LTE modem; LTE / HSPA+ Cat 4; Cellular certifications: PTCRB, RED, Europe
1002-CMF4-OUS	Digi CORE plug-In LTE modem; LTE / HSPA+ Cat 4, 3G fallback; Visit: https://www.digi.com/resources/certifications for latest certifications
1002-CMG4-GLB	Digi CORE plug-In LTE modem; Global LTE Cat 4, 3G / 2G fallback; Visit: https://www.digi.com/resources/certifications for latest certifications
ASB-1002-CM06-GLB	Digi CORE plug-In LTE modem; LTE-A / HSPA+ Cat 6; Cellular certifications: PTCRB, RED, AT&T, Verizon, Canada, Europe
ASB-1002-CM16-GLB	Digi CORE plug-In LTE modem; LTE-A / HSPA+ Cat 6; Cellular certifications: Australia / New Zealand
ASB-1003-CM11-GLB	Digi CORE plug-In LTE modem; LTE-A / HSPA+ Cat 11; Cellular certifications: PTCRB, RED, AT&T, Verizon, Canada, Europe
ASB-1003-CM18-GLB	Digi CORE plug-In LTE modem; LTE-A Pro / HSPA+ Cat 18; Cellular certifications: PTCRB, AT&T, Verizon, US, Canada, Europe
ASB-1003-CM18-OUS	Digi CORE plug-In LTE modem; FirstNet Ready LTE-A Pro / HSPA+ Cat 18; Cellular certifications: PTCRB, AT&T, Verizon, Canada

FOR MORE INFORMATION
PLEASE VISIT **DIGI.COM**

*FirstNet® and FirstNet Ready™ are registered trademarks and service marks of the First Responder Network Authority.

DIGI SERVICE AND SUPPORT / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit www.digi.com/support.

© 1996-2021 Digi International Inc. All rights reserved.
All trademarks are the property of their respective owners.

DIGI INTERNATIONAL WORLDWIDE HQ
877-912-3444 / 952-912-3444 / www.digi.com

DIGI INTERNATIONAL JAPAN
+81-3-5428-0261 / www.digi-intl.co.jp

DIGI INTERNATIONAL GERMANY
+49-89-540-428-0

DIGI INTERNATIONAL SINGAPORE
+65-6213-5380

DIGI INTERNATIONAL CHINA
+86-21-50492199 / www.digi.com.cn



C6/121
91004367